



SILICONE (300 MICRON)


3001
White



3002
Black



3003
Royal Blue




3004
Yellow



3005
Red




3006
Gray




3007
Dark Gray




3008
Neon Yellow




3009
Neon Orange



3010
Neon Pink



3011
Neon Green



3012
Neon Blue




3014
Gold



3015
Silver

SILICONE (600 MICRON)

6001
White



6002
Black

SILICONE

DESCRIPTION

SILICONE 300 - Only for plotter cutting
SILICONE 600 - Laser and plotter cutting application

SPECIFICATION

SILICONE 300
Size: 50 cm x 25 m
N.W: 6 kg / roll

SILICONE 600
Size: 50 cm x 25 m
N.W: 9,5 kg / roll

TRANSFER CONDITION

The following instructions are given as guideline only.
Temperature: 165°C (329°F)
Pressing Time: 15 seconds

SUITABLE FOR

Cotton, mixtures of polyester / cotton and polyester / acrylic or for similar textile.
Not suitable for treated and dyed garments.

NOTICE

We offer you to test the product against the color migration.
Pressing instruction may change, according to the fabric type.

ÜRÜN TANIMI

SILICONE 300 - Sadece plotter kesim
SILICONE 600 - Lazer ve plotter kesim uyg. için malzeme

ÖZELLİKLER

SILICONE 300
Ebat: 50 cm x 25 m
Net Ağırlık: 6 kg / roll

SILICONE 600
Ebat: 50 cm x 25 m
Net Ağırlık: 9,5 kg / roll

BASKI TALİMATLARI

Aşağıdaki talimatlar sadece normal şartlara göredir.
Derece: 165°C (329°F)
Baskı Süresi: 15 saniye

UYGUN KUMAŞLAR


Pamuk, polyester / pamuk karışımı, polyester / akrilik vb tekstiller için uygundur.
Boyanmış ve işlem görmüş kumaşlar için uygun değildir.

UYARI


Boyalı kumaşlarda migrasyon ihtimaline karşı üretim öncesi gerekli testlerin yapılmasını öneririz. Kullanılacak kumaşın içeriğine göre, basım talimatları değişebilir.



Cut the image in reverse
Deseni tersten kesiniz




165°C (329°F)





4 Bar pressure
4 Bar basınç



15 seconds for pressing
15 saniye presleme



COLD Peel
Soğuk çekim



After 24H with application
Uygulamadan 24 saat sonra